

3nh produced good instrument

Haze meter/Transmittance meter YH1200 technical features:

- In line with international standards
- Built-in Φ154mm integrating sphere
- D65, A, C three light sources
- Support haze and transmittance measurement





Dual Array Silicon Photonics Diode sensor



Spectral display


















Product description

YH1200 haze meter can easily achieve ASTM D1003 non-compensation method, full light transmittance,haze test. Open sample bin can be vertically and horizontally tested to accommodate more samples to be tested. The YH1200 haze meter uses a PDF array detector to meet the CIE V(λ)2 degree visual response. The compensation method can be used to measure the light transmittance and haze with high precision and repeatability.







Meet a variety of test requirements, Standards compliant: ASTM D1003/1044, ISO 14782, GB/T 2410, JJF 1303-2011, CIE 15.2, JJS K7105, JJS K7361, JJS K7136

Simple operation and quick measurement

The YH1200 haze meter is equipped with a large-size touch screen for easy operation. With a PD array detector, CIE $V(\lambda)$ 2 degree visual response enables high precision and repeatable transmittance and fog measurements. USB data output device for docking with laboratory system.

Dynamic measurement

Independent light source detector and temperature sensor, constantly monitor light source and environmental change, ensure the reliability of test data.

Support a variety of samples

Independent light source detector and temperature sensor, constantly monitor light source and environmental change, ensure the reliability of test data.

Support a variety of samples

It provides powerful software for measuring and analyzing fog and light transmittance, which is suitable for quality monitoring and tabulated management of fog and light transmittance data in various industries. The management of users will be digitized at the PC end, the difference of fog and light transmittance will be compared, and the test report form will be generated to facilitate customer customization and management.

Model: YH1200

Optical Geometry: Transmission: 0/D (parallel light illumination, diffuse reflection reception)

Standards compliant: ASTM D1003/1044,ISO 13468,ISO 14782,GB/T 2410,JJF 1303-2011,CIE 15.2,JIS K7105,JIS K7361,JIS K7136

Integrating Sphere Size: Ф 154mm Illuminant: 400-700nm LED light source

Spectrophotometric Mode: /

Sensor: PD array detector, meeting CIE $V(\lambda)$ 2 degree visual response

Wavelength Range: / Wavelength Pitch: / Semiband Width: /

Transmittance range: 0-100%

Measuring Aperture: Φ20mm/Φ15mm/Φ8mm/Φ4mm(Choose one)

Sample size: The thickness is less than 170mm

Color Space: /

Color Difference Formula: /

Other Colorimetric Data: Haze(ASTM D1003/1044,ISO 13468), Transmittance T(ISO), Transmittance T(ASTM)

Observer Angle: 2° Illuminants: D65,A,C

Displayed Data: Pass/fail result Measuring Time: about 1.5s

Precision: 0.01

Repeatability: \$\Phi 20 \text{ mm aperture, less than 0.05 (after instrument preheating and correction, test the standard nebulizer with the

nebulization of about 30 at an interval of 5s for 30 times of standard deviation)

Inter-instrument Error: \$\phi_{20mm}\$ Caliber.< 0.4

(After the instrument is warmed up and corrected, test the standard deviation of the haze standard haze sheet and the reference value at an interval of 5s)

Size: Length X Width X Height=290x211x511mm

Weight: About 7.6 kg

Power Supply: DC 24V, 3A Power Adapter

Light Source Device Life: 5 years, more than 3 million times measurements.

Display: 7" TFT Capacitive Screen-touch Display

Data Port: USB & Print serial port

Data Storage: Standard 1000 Pcs, Sample 20000 Pcs Language: Simplified Chinese, Traditional Chinese, English

Working Environment: Temperature: 0~40°C; Humidity: 0~85% (No Condensation) Storage Environment: Temperature: -20~50°C; Humidity: 0~85% (No Condensation)

Standard Accessory: Power adapter, manual, quality management software (download from official website), data cable, 0% calibration box, measuring caliber

Optional Accessory: Micro printer, test fixture, standard haze film, foot switch

Notes: The specifications are subject to change without notice.

GUANGDONG THREENH TECHNOLOGY CO., LTD.
























Email:3nh@3nh.com





Add: 6-8th floors, Building B33, Low Carbon Headquarters Park, Xincheng Road No.400, Zengcheng District, Guangzhou, Guangdong Province, China